



## Anterior (upper and lower)





# Satin-Steel™ Rubberdam Clamps


## Premolars (upper and lower)




## Upper Molars



## Lower Molars



## Molars (upper and lower)




Manufacturer: Hu-Friedy Mfg. Co., Inc. · 3232 N. Rockwell Street · Chicago, IL 60618 · USA

EC Representative: Hu-Friedy Mfg. Co., Inc., Zweigniederlassung Deutschland  
Rudolf-Diesel-Straße 8 · D-69181 Leimen · Tel. +49 (0) 62 24 / 97 00-0  
Fax 97 00-97 · E-Mail: info@hu-friedy.de · www.hu-friedy.de

Suggested applications. Use for a specific case is dependent on the clinical judgement of the dental professional. Hang this poster in your office for easy reference and reordering. All clamps shown 80% size.

**Hu-Friedy**



Satin-Steel™  
Rubberdam Clamps

Part Code	Recognized	Number	Part Code
RDCM12A+	12A		RDCM12A
RDCM13A+	13A		RDCM13A
RDCM14	14		RDCM14
RDCM14A	14A		RDCM14A
RDCM14*	W14		RDCM14
RDCM14A	W14A		RDCM14A
RDCM18	-		RDCM18
RDCM24	-		RDCM24
RDCM25	-		RDCM25
RDCM26	26		RDCM26
RDCM26N	26N		RDCM26
RDCM27	27		RDCM27
RDCM27N	27N		RDCM27
RDCM28	28N		RDCM28
RDCM29	-		RDCM29
RDCM30	-		RDCM30
RDCM31	-		RDCM31
RDCM56	56		RDCM56
RDCM56S	56T		RDCM56S
RDCM56*	W56		RDCM56*
RDCM201	-		RDCM201
RDCM205	-		RDCM205
RDCM209*	209		RDCM209*
RDCM212	212		RDCM212
RDCM212SA	212SA		RDCM212
RDCM212UNC**	-		RDCM212U
RDCM212SA without picture	-		RDCM212U
planned in wingless version	-		RDCM212U

Part Code	Recognized	Number	Part Code
RDCM12A+	12A		RDCM12A
RDCM13A+	13A		RDCM13A
RDCM14	14		RDCM14
RDCM14A	14A		RDCM14A
RDCM14*	W14		RDCM14
RDCM14A	W14A		RDCM14A
RDCM18	-		RDCM18
RDCM24	-		RDCM24
RDCM25	-		RDCM25
RDCM26	26		RDCM26
RDCM26N	26N		RDCM26
RDCM27	27		RDCM27
RDCM27N	27N		RDCM27
RDCM28	28N		RDCM28
RDCM29	-		RDCM29
RDCM30	-		RDCM30
RDCM31	-		RDCM31
RDCM56	56		RDCM56
RDCM56S	56T		RDCM56S
RDCM56*	W56		RDCM56*
RDCM201	-		RDCM201
RDCM205	-		RDCM205
RDCM209*	209		RDCM209*
RDCM212	212		RDCM212
RDCM212SA	212SA		RDCM212
RDCM212UNC**	-		RDCM212U
RDCM212SA without picture	-		RDCM212U
planned in wingless version	-		RDCM212U

Part Code	Recognized	Number	Part Code
RDCM0	0		RDCM0
RDCM00	00		RDCM00
RDCM00	00		RDCM00
RDCM1	1		RDCM1
RDCM1A	1A		RDCM1A
RDCM2	2		RDCM2
RDCM2	W2		RDCM2
RDCM2A	2A		RDCM2A
RDCM2A*	W2A		RDCM2A*
RDCM2AS	2AT		RDCM2AS
RDCM3	3		RDCM3
RDCM3	W3		RDCM3
RDCM4	4		RDCM4
RDCM4	W4		RDCM4
RDCM5	5		RDCM5
RDCM6	6		RDCM6
RDCM7	7		RDCM7
RDCM7	W7		RDCM7
RDCM7A	7A		RDCM7A
RDCM8	8		RDCM8
RDCM8A	8A		RDCM8A
RDCM8A	W8A		RDCM8A
RDCM8AD	-		RDCM8AD
RDCM9	9		RDCM9
RDCM9S	9T		RDCM9S
RDCM10	10		RDCM10
RDCM11	11		RDCM11
RDCM11	-		RDCM11
RDCM11	W8A		RDCM11
RDCM11	N/A		RDCM11
RDCM205	-		RDCM205
RDCM209*	209		RDCM209*
RDCM212	212		RDCM212
RDCM212SA	212SA		RDCM212
RDCM212UNC**	-		RDCM212U
RDCM212SA without picture	-		RDCM212U
planned in wingless version	-		RDCM212U

Part Code	Recognized	Number	Part Code
RDCM12A+	12A		RDCM12A
RDCM13A+	13A		RDCM13A
RDCM14	14		RDCM14
RDCM14A	14A		RDCM14A
RDCM14*	W14		RDCM14
RDCM14A	W14A		RDCM14A
RDCM18	-		RDCM18
RDCM24	-		RDCM24
RDCM25	-		RDCM25
RDCM26	26		RDCM26
RDCM26N	26N		RDCM26
RDCM27	27		RDCM27
RDCM27N	27N		RDCM27
RDCM28	28N		RDCM28
RDCM29	-		RDCM29
RDCM30	-		RDCM30
RDCM31	-		RDCM31
RDCM56	56		RDCM56
RDCM56S	56T		RDCM56S
RDCM56*	W56		RDCM56*
RDCM201	-		RDCM201
RDCM205	-		RDCM205
RDCM209*	209		RDCM209*
RDCM212	212		RDCM212
RDCM212SA	212SA		RDCM212
RDCM212UNC**	-		RDCM212U
RDCM212SA without picture	-		RDCM212U
planned in wingless version	-		RDCM212U

## HU-FRIEDY SATIN STEEL™ CROSS REFERENCE CHART

**Satin STEEL™**

Matte-finish Satin Steel™ clamps reduce glare and improve field of vision.



Our Satin Steel™ rubber dam clamps are created with a very bright beginning - each one is carefully designed and handcrafted for superior strength and corrosion resistance. The dull, matte-finish comes next.

In order to improve vision in the operatory area, today's dental lighting is brighter and more intense than ever before. But shiny rubber dam clamps may actually reduce visibility by reflecting this light back into your eyes, creating a blinding glare. Magnification from loupes or microscopes can intensify the glare even further.


Satin Steel™ clamps from Hu-Friedy are the perfect partner to bright clinical lighting. They have a dull, matte finish which absorbs and dissipates harsh light instead of reflecting it. The result is a clear, comfortable field of vision more comfortable for you.

For more information please contact your Hu-Friedy dealer or Hu-Friedy directly.

**Hu-Friedy**

Manufacturer: Hu-Friedy Mfg. Co., Inc.  
3232 N. Rockwell Street · Chicago, IL 60618 · USA

EC Representative: Hu-Friedy Mfg. Co., Inc.,  
Zweigniederlassung Deutschland  
Rudolf-Diesel-Straße 8 · D-69181 Leimen  
Tel. +49 (0) 62 24 / 97 00-0 · Fax 97 00-97  
E-Mail: info@hu-friedy.de · www.hu-friedy.de



The basic items **RDAF6** (Frame), **RDTFDI** (Template FDI), **RDTUNIV** (Template universal), **RDCOB**, **RDF**, **RDP**, and **Rubber Dam Clamps 0, 1, 2, 7, 8, 8A, 14A and 212** needed for rubber dam procedures conveniently packaged in a kit.




Rubberdam Board  
Keeps clamps easily accessible at chairside and organized throughout cleaning and sterilization. Eight pegs securely hold various sized clamps.



RDF

Rubber Dam Forceps



RDP

Rubber Dam Punch

RDAF6

Frame Adults

RDCF5

Frame Children